



SEALING SOLUTIONS FOR HYDROGEN SERVICES



For the highest rated, safest solution on the market, look no further than the **EVOLUTION**[®] gasket.

Due to its unrivalled sealing performance, **EVOLUTION**[®] is a gasket designed for hydrogen applications. Hydrogen provides a number of unique challenges which have a direct impact on sealing, and the materials used in these applications must be suitable for the challenge.

GPT[®]
Industries

4990 Iris Street, Wheat Ridge, CO 80033
TEL: (303) 988-1242
FAX: (303) 988-1922
www.gptindustries.com

GPT[®]
Industries

THE CHALLENGES SPECIFIC TO HYDROGEN INCLUDE:

Sealing capabilities – hydrogen has a high propensity to leak.

The reason for this is because of its:

- Low viscosity.
- Very high diffusivity.
- Likelihood of embrittlement.
- Smallest molecule gas.

Permeation – permeation leads to 2 major challenges:

- Hydrogen gas could potentially permeate all the way through the material itself, leading to leaks. So even if the seals are doing their job, emissions can still occur through the material.
- Permeation is what can lead to embrittlement. Embrittlement can cause:
 - Mechanical stress cracking.
 - Hydrogen induced cracking.
 - Stress oriented hydrogen induced cracking.
 - High temperature hydrogen damage.
- All of these crackings take place within a metal substrate. The rub lies in that metallic seals are likely to be used to avoid leaks from permeation, as gas will not permeate all the way through the material. However, these metals are now susceptible to embrittlement. Essentially, hydrogen is absorbed by the metal, which reduces yield strength and leads to premature failure.

Propensity to ignite and consequences of fire and explosion:

- Wide flammability range.
- Very low ignition energy.
- Spontaneous ignition.

Chemical compatibility:

- Hydrogen soaking can reduce functional strength of materials.
- Other medias can be present in hydrogen lines that a seal needs to be chemically compatible with, such as CO₂, amines, steam, H₂S.

Overall safety:

- Limited regulations to date.
- Limited testing to date.
- There are real and perceived dangers to hydrogen, and if something were to happen this would have a huge impact. Sealing plays a major role in this function.

THE SEALING SOLUTION TO HYDROGEN CHALLENGES:

GPT's **EVOLUTION**[®] gasket brings a sealing solution to hydrogen service by mitigating each of these challenges:

- **EVOLUTION**[®] is the lowest emission gasket in the industry. The sealing of **EVOLUTION**[®] utilizes a dual seal design, with both seals – a PTFE seal and Inconel C-Ring – being top of their class in sealing. These seals work independently, creating a level of redundancy to create top level sealing, even in small molecule gases such as hydrogen. This has been shown in Shell TAT testing, Chevron CFET testing, API PR2 testing, and more.
- The **EVOLUTION**[®] gasket has been testing to over 20,000 psi without leakage.
- **EVOLUTION**[®] utilizes a metal core and metal secondary C-Ring seal. As a result of these, there is no permeation that can occur through the gasket itself.
- Even though these metallic elements are present, there is no exposed metal to the media. Both the metal core and C-Ring seal are completely encapsulated in coating. In addition, sealing will occur inboard of by the PTFE seal, protecting the metallic elements from seeing the media.
- PTFE is a recommended ID seal option as this material is designed to provide less permeation than elastomer-bound seals.
- **EVOLUTION**[®] is inherently a fire safe gasket.
- Successfully passed the API 6FB fire test in sizes 6" 300#, 2" 2500#, 12" 600#, and 24" 300#.
- Due to utilizing a PTFE ID seal, **EVOLUTION**[®] provides chemical compatibility beyond typical metallic and elastomeric gaskets.

- Chemical compatibility for (among others):

- Hydrogen.
- CO₂.
- Amines.
- Steam.
- H₂S.
- Ammonia.

- Our restructured PTFE has been BAM tested for storage in Hydrogen.

evolution[®]

